



SL2011539010



**External corner VDI for trunking tehalit.SL 20x115mm pure white**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Dimensions**

Trunking height 115 mm

Trunking width 20 mm

**Cover, door**

Lid with softlip No

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Settings**

Angle range 83 / 135 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHs voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature 5...60 °C

**temperatur**

Ambient temperature 5...60 °C