




SL2011589010



T-piece for trunking tehalit.SL 20x55mm pure white

Technical properties

Dimensions

Trunking height	115 mm
Trunking width	20 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Equipment

Trunking adapter (to adopt to a skirting trunking)	Leitungsführungskanal
--	-----------------------

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------