



SLA180750ELN



Floortrack 18x75,anodised

Technical properties

Configuration

Antibacterial treatment	No
Self-adhesive	No

Dimensions

Trunking height	18 mm
Length	2000 mm
Trunking width	73 mm
Width of installed product	73 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	4
Maximum number of cables (Ø 11 mm, 50% fill)	4

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	mixed material
Type of surface treatment	untreated

Equipment

Number of fix dividers	3
Compartment quantity	4
Number of channels	4

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK10

temperatur

Ambient temperature	-5...65 °C
---------------------	------------