



SM150

Analogue ammeter 0-150A indirect reading

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Measurement scale	150 A
-------------------	-------

Voltage

Rated insulation voltage	2000 V
--------------------------	--------

Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

Power

Power consumed	1.1 VA
----------------	--------

Total power loss under IN	1.1 W
---------------------------	-------

Installation, mounting

Modular version	Yes
-----------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------