



SM200

Pulsed output module for SM102E

Technical properties

Main electrical features

| | |
|-----------|------|
| Frequency | - Hz |
|-----------|------|

Voltage

| | |
|--------------------------|------|
| Rated insulation voltage | 4 kV |
|--------------------------|------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 36 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 84 mm |
|-----------------------------|-------|

| | |
|--------|-------|
| Length | 49 mm |
|--------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 21 mm |
|----------------------------|-------|

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,5 / 1,5mm ² |
|---|--------------------------|

| | |
|------------------------------------|--------------------------|
| Connection cross-sect. rigid cable | 0,5 / 1,5mm ² |
|------------------------------------|--------------------------|

| | |
|--------------------|------------|
| Type of connection | with screw |
|--------------------|------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|----|
| Halogen free | No |
|--------------|----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...55 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -20...80 °C |
|-------------------------------|-------------|