



SM201

Pulsed output module for SM103E

Technical properties

Architecture

Fixing mode	Clamping and screwable
-------------	------------------------

Voltage

Rated insulation voltage	4 kV
--------------------------	------

Dimensions

Depth of installed product	36 mm
Height of installed product	84 mm
Length	49 mm
Width of installed product	21 mm

Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 1,5mm ²

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-20...80 °C