



SM201

## Pulsed output module for SM103E

### Technical properties

#### Main electrical features

Frequency	- Hz
-----------	------

#### Voltage

Rated insulation voltage	4 kV
--------------------------	------

#### Dimensions

Depth of installed product	36 mm
----------------------------	-------

Height of installed product	84 mm
-----------------------------	-------

Length	49 mm
--------	-------

Width of installed product	21 mm
----------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm <sup>2</sup>
---	--------------------------

Connection cross-sect. rigid cable	0,5 / 1,5mm <sup>2</sup>
------------------------------------	--------------------------

Type of connection	with screw
--------------------	------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-20...80 °C
-------------------------------	-------------