



SM202



## 2 Inputs / 2 Outputs module for SM103E

### Technical properties

#### Main electrical features

Frequency - Hz

#### Voltage

Rated insulation voltage 4 kV

#### Dimensions

Depth of installed product 36 mm

Height of installed product 84 mm

Length 49 mm

Width of installed product 21 mm

#### Connection

Connection cross-sect. flexible conductor 0,5 / 1,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,5 / 1,5mm<sup>2</sup>

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

#### Use conditions

Operating temperature -10...55 °C

Storage/transport temperature -20...80 °C