



SM203

Analogue output module for SM103E

Technical properties

Main electrical features

Frequency	- Hz
-----------	------

Voltage

Rated insulation voltage	4 kV
--------------------------	------

Dimensions

Depth of installed product	36 mm
----------------------------	-------

Height of installed product	84 mm
-----------------------------	-------

Length	49 mm
--------	-------

Width of installed product	21 mm
----------------------------	-------

Connection

Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
---	--------------------------

Connection cross-sect. rigid cable	0,5 / 1,5mm ²
------------------------------------	--------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-20...80 °C
-------------------------------	-------------