



SM205

Unit T°C for SM103E

Technical properties

Main electrical features

Frequency - Hz

Voltage

Rated insulation voltage 4 kV

Dimensions

Depth of installed product 36 mm

Height of installed product 84 mm

Length 49 mm

Width of installed product 21 mm

Connection

Connection cross-sect. flexible conductor 0

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature -10...55 °C

Storage/transport temperature -20...80 °C