



SM401

## Digital ammeter 0-400A indirect reading

### Technical properties

#### Functions

Precision class	1%
-----------------	----

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Measurement scale	400 A
-------------------	-------

#### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

Frequency	45/65 Hz
-----------	----------

#### Voltage

Voltage drop	120 mV
--------------	--------

#### Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

#### Power

Power consumed	1 VA
----------------	------

Total power loss under IN	1 W
---------------------------	-----

#### Installation, mounting

Modular version	Yes
-----------------	-----

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
---	------------------

Connection cross-sect. rigid cable	10mm <sup>2</sup>
------------------------------------	-------------------

#### Equipment

Digits number	3
---------------	---

#### Safety

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-40...70 °C
-------------------------------	-------------