



SM501

Digital voltmeter

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	70 mm

Power

Power consumed	3.5 VA
Total power loss under IN	3.5 W

Measurement

Voltage measurement range	0 to 500 V
Type of measuring instrument	voltmeter

Installation, mounting

Mounting type	din-Rail
---------------	----------

Equipment

Digits number	3
---------------	---

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-40...70 °C