



SM501

Digital voltmeter

Technical properties

Functions

Precision class	1%
-----------------	----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	45/65 Hz
-----------	----------

Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

Power

Power consumed	3.5 VA
----------------	--------

Total power loss under IN	3.5 W
---------------------------	-------

Measurement

Voltage measurement range	0 to 500 V
---------------------------	------------

Type of measuring instrument	voltmeter
------------------------------	-----------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	6mm ²
---	------------------

Connection cross-sect. rigid cable	10mm ²
------------------------------------	-------------------

Type of connection	with screw
--------------------	------------

Equipment

Digits number	3
---------------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-40...70 °C
-------------------------------	-------------