



SP040D

Cartridge 40kA 275V for pluggable SPD

Technical properties

Architecture

Number of poles 1 P

Configuration

Number of modules 1

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 15 kA

Voltage

Maximum continuous operating voltage U_c 275 V

Voltage protection level U_p according to IEC61643-1 1.3 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 40 kA

Dimensions

Width of installed product 0 mm

Power

Total power loss under I_N 0 W

Standards

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE not concerned

Use conditions

Operating temperature -20...60 °C

Degree of pollution according to IEC 60664 / IEC 60947-2 2

Storage/transport temperature -40...80 °C