



SP040D

**Cartridge 40kA 275V for pluggable SPD**

**Technical properties**

**Architecture**

Number of poles 1 P

**Configuration**

Number of modules 1

**Main electrical features**

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE 15 kA

**Voltage**

Maximum continuous operating voltage Uc 275 V

Voltage protection level Up according to IEC61643-1 1.3 kV

**Electric current**

Max discharge (Imax) L-N(PEN)/ N-PE 40 kA

**Dimensions**

Width of installed product 0 mm

**Power**

Total power loss under IN 0 W

**Standards**

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE not concerned

**Use conditions**

Operating temperature -20...60 °C

Storage/transport temperature -40...80 °C