



SP120

SPD 1P monobloc 50kA class 1

Technical properties

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	50 kA
-------------------------------------	-------

Dimensions

Width of installed product	36 mm
----------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Network configuration

Network type	TT/TN
--------------	-------

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	35mm ²
Connection cross-sect. rigid cable	50mm ² max.

Standards

Test class IEC61643-11 / VDE0675-6-11	T1
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C