



SPB008D

Cartridge L-N Uc 275 In 2kA I_{max} 8kA U_p 1kV

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U _e	240 / 415 V
Frequency	50/60 Hz

Voltage

Maximum continuous operating voltage U _c	275 V
---	-------

Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm

Electrical specifications

Short-circuit breaking capacity (I _{sc} cr)	25 kA
--	-------

Installation, mounting

Tightening torque	3
-------------------	---

Connection

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm ²

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------