



SPB040N

Cartridge N-PE Uc 260V In 20kA I_{max} 40kA Up 1.5kV

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U _e | 240 / 415 V |
| Frequency | 50/60 Hz |

Voltage

| | |
|---|-------|
| Maximum continuous operating voltage U _c | 260 V |
|---|-------|

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 58.2 mm |
| Height of installed product | 89.8 mm |

Electrical specifications

| | |
|--|-------|
| Short-circuit breaking capacity (I _{sc} cr) | 25 kA |
|--|-------|

Installation, mounting

| | |
|-------------------|---|
| Tightening torque | 3 |
|-------------------|---|

Connection

| | |
|--|--------------------------|
| Connection cross-section of input and output with screws, for massive conductors | 1.5 / 35 mm ² |
| Connection cross section of access and exit with screws, for flexible conductor | 1.5 / 25 mm ² |

Standards

| | |
|---------------------------------------|-----------|
| Test class IEC61643-11 / VDE0675-6-11 | T2 |
| European directive WEEE | concerned |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -40...80 °C |
|-----------------------|-------------|