



SPB065R

## Cartridge L-N Uc 320V In 20kA I<sub>max</sub> 65kA Up 1,35kV

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Controls and indicators

Indicator lamp	Optic
----------------	-------

#### Main electrical features

Rated operational voltage U <sub>e</sub>	240 / 415 V
Frequency	50/60 Hz

#### Voltage

Maximum continuous operating voltage U <sub>c</sub>	320 V
Voltage protection level U <sub>p</sub> according to IEC61643-1	1.45 kV

#### Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm

#### Electrical specifications

Short-circuit breaking capacity (I <sub>sc</sub> cr)	25 kA
--	-------

#### Installation, mounting

Tightening torque	3
-------------------	---

#### Connection

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm <sup>2</sup>

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------