



SPK700

## Surge protection IT for satellite TV

### Technical properties

#### Configuration

Earthing via Separate conductor

#### Controls and indicators

Indicator lamp no

#### Main electrical features

Rated operational voltage Ue 14 / 18 V DC

#### Voltage

Maximum continuous operating voltage U<sub>c</sub> 20 V

Rated operational voltage in DC 20 V

Voltage protection level U<sub>p</sub> according to IEC61643-1 500 V

Maximum continuous operating voltage U<sub>c</sub> DC IEC61643 20 V

#### Dimensions

Depth of installed product 71.5 mm

Height of installed product 31.5 mm

Width of installed product 144.9 mm

Width 144.9 mm

#### Frequency

Frequency 50 to 60 Hz

#### Installation, mounting

Tightening torque 0.5Nm

Mounting type din-Rail

#### Connection

Type of connection terminal standard "F" for coaxial cable

#### Standards

Approvals CE, KEMA

Test class IEC61643-11 / VDE0675-6-11 B2 ; C1 ; C2 ; C3 ; D1

European directive WEEE concerned

#### Use conditions

Operating temperature -40...85 °C

Storage/transport temperature -40...80 °C