



SPK700

Surge protection IT for satellite TV

Technical properties

Configuration

Earthing via Separate conductor

Controls and indicators

Indicator lamp no

Main electrical features

Rated operational voltage Ue 14 / 18 V DC

Voltage

Maximum continuous operating voltage U_c 20 V

Rated operational voltage in DC 20 V

Voltage protection level U_p according to IEC61643-1 500 V

Maximum continuous operating voltage U_c DC IEC61643 20 V

Dimensions

Depth of installed product 71.5 mm

Height of installed product 31.5 mm

Width of installed product 144.9 mm

Width 144.9 mm

Frequency

Frequency 50 to 60 Hz

Installation, mounting

Tightening torque 0.5Nm

Mounting type din-Rail

Connection

Type of connection terminal standard "F" for coaxial cable

Standards

Approvals CE, KEMA

Test class IEC61643-11 / VDE0675-6-11 B2 ; C1 ; C2 ; C3 ; D1

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature	-40...85 °C
Storage/transport temperature	-40...80 °C
