



SPN080

Cartridge 25kA class 1 for SPN8xxx

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	25 kA
--	-------

Power

Total power loss under I _N	0 W
---------------------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T1
---------------------------------------	----

Use conditions

Operating temperature	-40...60 °C
Storage/transport temperature	-40...80 °C