



SPN080N

Cartridge neutral 25kA class 1 for SPN802 and SPN802R

Technical properties

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Test class type1 IEC61643-11	Yes
------------------------------	-----

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	25 kA
-------------------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T1
---------------------------------------	----

Use conditions

Operating temperature	-40...60 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------