



SPN115R

## SPD 1P pluggable 15kA class 2 with reserve + remote contact

### Technical properties

#### Architecture

Type of pole 1 P

#### Configuration

Number of modules 1

#### Controls and indicators

Indicator lamp reserve

#### Main electrical features

Rated operational voltage  $U_e$  230 / 400 V

Frequency 50/60 Hz

Nominal discharge current ( $I_n$ ) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE 5 kA

#### Voltage

Maximum continuous operating voltage  $U_c$  275 V

Voltage protection level  $U_p$  according to IEC61643-1 1 kV

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 15 kA

#### Power

Total power loss under  $I_N$  0 W

#### Installation, mounting

Tightening torque 3,6Nm

#### Connection

Connection cross-sect. flexible conductor 25mm<sup>2</sup>

Connection cross-sect. rigid cable 35mm<sup>2</sup>

#### Standards

Test class IEC61643-11 / VDE0675-6-11 T2

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Use conditions

Operating temperature -40...55 °C

