



SPN408S

SPD 4P monobloc 8kA class 2 with light indicator

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage U_e	230 / 400 V
Frequency	50/60 Hz
Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	2 kA

Voltage

Maximum continuous operating voltage U_c	255 V
Voltage protection level U_p according to IEC61643-1	1 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE	8 kA
--	------

Dimensions

Width of installed product	54 mm
----------------------------	-------

Power

Total power loss under I_N	0 W
------------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	not concerned

Use conditions

Operating temperature	-40...60 °C
Storage/transport temperature	-40...80 °C