



SPN802R

**SPD 4P pluggable 100kA class 1 with end of life indicator and remote contact TT**

**Technical properties**

**Configuration**

Number of modules	8
-------------------	---

**Controls and indicators**

Indicator lamp	end of life indicator
----------------	-----------------------

**Main electrical features**

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz

**Electric current**

Max discharge (Imax) L-N(PEN)/ N-PE	100 kA
-------------------------------------	--------

**Dimensions**

Depth of installed product	83 mm
Width of installed product	144 mm

**Power**

Total power loss under IN	0 W
---------------------------	-----

**Network configuration**

Network type	TT
--------------	----

**Installation, mounting**

Tightening torque	3,6Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	35mm <sup>2</sup>
Connection cross-sect. rigid cable	35mm <sup>2</sup>

**Standards**

Test class IEC61643-11 / VDE0675-6-11	T1
---------------------------------------	----

**Use conditions**

Operating temperature	-40...60 °C
Storage/transport temperature	-40...80 °C