



SPV025E

**Cartridge earth for SPV325**

**Technical properties**

**Architecture**

Type of pole PE

**Configuration**

Number of modules 1

**Controls and indicators**

Indicator lamp reserve

**Main electrical features**

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE 12.5 kA

**Voltage**

Maximum continuous operating voltage Uc 1000 V

Voltage protection level Up according to IEC61643-1 4 kV

**Electric current**

Max discharge (Imax) L-N(PEN)/ N-PE 25 kA

**Dimensions**

Width of installed product 18 mm

**Power**

Total power loss under IN 0 W

**Standards**

Test class IEC61643-11 / VDE0675-6-11 T2

**Use conditions**

Operating temperature -40...80 °C

Storage/transport temperature -40...80 °C