



SPV025E

### Cartridge earth for SPV325

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Controls and indicators

Indicator lamp	reserve
----------------	---------

#### Main electrical features

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	12.5 kA
-----------------------------------------------------------------------	---------

#### Voltage

Maximum continuous operating voltage Uc	1000 V
Voltage protection level Up according to IEC61643-1	4 kV

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	25 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	18 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

#### Use conditions

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C