



ST301

## Bell transformer 4VA 230/8-12V

### Technical properties

#### Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4000 V
Output voltage 2	12 V
Output voltage	8 / 12 V

#### Electric current

Output intensity 2	0.33 A
Output intensity	0.5 A

#### Dimensions

Depth of installed product	65 mm
Height of installed product	111 mm
Width of installed product	35 mm

#### Power

Power consumed	4 VA
Total power loss under IN	1.8 W

#### Installation, mounting

Suitable for surface mounting	Yes
Suitable for flush-mounting	No

#### Connection

Connection cross-sect. rigid cable	6mm <sup>2</sup>
------------------------------------	------------------

#### Equipment

On/Off switch	No
Short-circuit protected	Yes

#### Standards

European directive WEEE	concerned
-------------------------	-----------

**Safety**

---

Protection index IP

IP20

**Use conditions**

---

Operating temperature

-20...35 °C