



ST305



Bell transformer 16VA 230V 8-12V

Technical properties

Architecture

Fixing mode DIN rail type O (symmetrical)

Configuration

Number of modules 3

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Voltage

Rated insulation voltage 4000 V

Output voltage 2 12 V

Output voltage 8 / 12 V

Electric current

Output intensity 2 1.33 A

Output intensity 2 A

Dimensions

Depth of installed product 65 mm

Height of installed product 111 mm

Width of installed product 54 mm

Power

Power consumed 16 VA

Total power loss under IN 1.8 W

Installation, mounting

Suitable for surface mounting Yes

Suitable for flush-mounting No

Equipment

On/Off switch No

Short-circuit protected Yes

Standards

Standard text EN 61558-2-6

European directive WEEE concerned

Safety

Use conditions

Operating temperature

-20...35 °C