



ST305



Bell transformer 16VA 230V 8-12V

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
Output voltage 2	12 V
Output voltage	8 / 12 V

Electric current

Output intensity 2	1.33 A
Output intensity	2 A

Dimensions

Depth of installed product	65 mm
Height of installed product	111 mm
Width of installed product	54 mm

Power

Power consumed	16 VA
Total power loss under IN	1.8 W

Installation, mounting

Tightening torque	1,2Nm
Suitable for surface mounting	Yes
Suitable for flush-mounting	No

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Equipment

On/Off switch	No
Short-circuit protected	Yes

Standards

Standard text	EN 61558-2-6
---------------	--------------

Use conditions

Operating temperature

-20...35 °C

Altitude

<= 2000 m