



ST305



## Bell transformer 16VA 230V 8-12V

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	4000 V
Output voltage 2	12 V
Output voltage	8 / 12 V

#### Electric current

Output intensity 2	1.33 A
Output intensity	2 A

#### Dimensions

Depth of installed product	65 mm
Height of installed product	111 mm
Width of installed product	54 mm

#### Power

Power consumed	16 VA
Total power loss under IN	1.8 W

#### Installation, mounting

Tightening torque	1,2Nm
Suitable for surface mounting	Yes
Suitable for flush-mounting	No

#### Connection

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

#### Equipment

On/Off switch	No
Short-circuit protected	Yes

#### Standards

Standard text	EN 61558-2-6
---------------	--------------

**Use conditions**

Operating temperature

-20...35 °C

Altitude

&lt;= 2000 m