



SU212



Bell 12V

Technical properties

Functions

Mode of operation	Sound signal : type D - duration of intermittent operation recommended : 5s ON / 15s OFF
-------------------	--

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	8 / 12 V
Type of supply voltage	AC

Electric current

Operating current	0.33 A
Rated current	0.33 A

Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

Frequency

Frequency	50 to 0 Hz
-----------	------------

Power

Power consumed	5 VA
Total power loss under IN	5 W

Materials

Material	polyamide
----------	-----------

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Equipment

Noise level	85 dB
-------------	-------

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C