



SU212



## Bell 12V

### Technical properties

#### Functions

Mode of operation

Sound signal : type D - duration of intermittent operation recommended : 5s ON / 15s OFF

#### Configuration

Number of modules

1

#### Main electrical features

Rated operational voltage Ue

8 / 12 V

Type of supply voltage

AC

#### Electric current

Operating current

0.33 A

Rated current

0.33 A

#### Dimensions

Depth of installed product

65 mm

Height of installed product

80 mm

Width of installed product

18 mm

#### Frequency

Frequency

50 to 0 Hz

#### Power

Power consumed

5 VA

Total power loss under IN

5 W

#### Materials

Material

polyamide

#### Connection

Connection cross-sect. flexible conductor

4mm<sup>2</sup>

Connection cross-sect. rigid cable

6mm<sup>2</sup>

#### Equipment

Noise level

85 dB

#### Use conditions

Operating temperature

-10...40 °C

Storage/transport temperature

-25...60 °C