



SU212



Bell 12V

Technical properties

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage U _e	8 / 12 V
Type of supply voltage	AC

Electric current

Operating current	0.33 A
Rated current	0.33 A

Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

Frequency

Frequency	50 to 0 Hz
-----------	------------

Power

Power consumed	5 VA
Total power loss under IN	5 W

Materials

Material	polyamide
----------	-----------

Equipment

Noise level	85 dB
-------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C