



SVN131

Green LED Indicator light 12/48V

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	12 / 48 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	2000 V

Dimensions

Depth of installed product	62 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	0.33 W
---------------------------	--------

Materials

Colour	green
--------	-------

Lighting control

Type of lamp	LED
--------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C