



SVN133

**Orange LED Indicator light 12/48V**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	12 / 48 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	250 V
Rated impulse withstand voltage	2000 V

**Dimensions**

Depth of installed product	62 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	0.33 W
---------------------------	--------

**Materials**

Colour	orange
--------	--------

**Lighting control**

Type of lamp	LED
--------------	-----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C