



TG029



Surge protection device, KNX

Technical properties

Architecture

Fixing mode	pluggable
-------------	-----------

Electric current

Rated current	6 A
---------------	-----

Connection

Conductor cross-section	0.75 mm ²
Type of connection	with plug-in terminals

Cable

Line length	≈ 200 mm
-------------	----------

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------