



TG500A

Battery powered smoke detector, white

Technical properties

Functions

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m

Connectivity

Connection mode	hard-wired
-----------------	------------

Dimensions

Dimensions (LLxwwxhh)	125 mm x 48 mm
-----------------------	----------------

Measurement

Detection Range	50 m ²
-----------------	-------------------

Battery

life of battery	4 years
Weak battery warning	Yes

Power supply

Supply Voltage	1 battery 9V 6LR61
----------------	--------------------

Scope of delivery

Rechargeable battery backup included	No
--------------------------------------	----

Equipment

Sounder volume	85 dB
----------------	-------

Standards

Number of homologation to standard EC	0786-CPD-20390
Q-Label certification	No

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------