



TG500A

**Battery powered smoke detector, white**

**Technical properties**

**Functions**

|                  |                   |
|------------------|-------------------|
| Operating type   | Stand alone       |
| Built-in sounder | Yes, 85 dB at 3 m |

**Connectivity**

|                 |            |
|-----------------|------------|
| Connection mode | hard-wired |
|-----------------|------------|

**Dimensions**

|                      |                |
|----------------------|----------------|
| Dimensions (LLxwxhh) | 125 mm x 48 mm |
|----------------------|----------------|

**Measurement**

|                 |                   |
|-----------------|-------------------|
| Detection Range | 50 m <sup>2</sup> |
|-----------------|-------------------|

**Battery**

|                      |         |
|----------------------|---------|
| life of battery      | 4 years |
| Weak battery warning | Yes     |

**Power supply**

|                |                    |
|----------------|--------------------|
| Supply Voltage | 1 battery 9V 6LR61 |
|----------------|--------------------|

**Scope of delivery**

|                                      |    |
|--------------------------------------|----|
| Rechargeable battery backup included | No |
|--------------------------------------|----|

**Equipment**

|                |       |
|----------------|-------|
| Sounder volume | 85 dB |
|----------------|-------|

**Standards**

|                                       |                |
|---------------------------------------|----------------|
| Number of homologation to standard EC | 0786-CPD-20390 |
| Q-Label certification                 | No             |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10...55 °C |
|-----------------------|-------------|