



TG501A

Mains powered smoke detector, white color

Technical properties

Functions

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m
Smoke switcher	No

Connectivity

Connection mode	hard-wired
Networkable	Yes

Dimensions

Dimensions (LLxwxhh)	125 mm x 48 mm
----------------------	----------------

Network voltage

With voltage indication	No
-------------------------	----

Measurement

Detection Range	50 m ²
-----------------	-------------------

Battery

life of battery	230V, 4-year back-up battery life with DURACELL PLUS 9 V alkaline battery
Weak battery warning	Yes

Power supply

Supply Voltage	Mains / alkaline battery 9V 6LR61
----------------	-----------------------------------

Scope of delivery

Rechargeable battery backup included	No
--------------------------------------	----

Equipment

Sounder volume	85 dB
----------------	-------

Standards

Number of homologation to standard EC	1772-CPD-008344
Q-Label certification	No

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------