



TG501A

**Mains powered smoke detector, white color**

**Technical properties**

**Functions**

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m
Smoke switcher	No

**Connectivity**

Connection mode	hard-wired
Networkable	Yes

**Dimensions**

Dimensions (LLxwxhh)	125 mm x 48 mm
----------------------	----------------

**Network voltage**

With voltage indication	No
-------------------------	----

**Measurement**

Detection Range	50 m <sup>2</sup>
-----------------	-------------------

**Battery**

life of battery	230V, 4-year back-up battery life with DURACELL PLUS 9 V alkaline battery
Weak battery warning	Yes

**Power supply**

Supply Voltage	Mains / alkaline battery 9V 6LR61
----------------	-----------------------------------

**Scope of delivery**

Rechargeable battery backup included	No
--------------------------------------	----

**Equipment**

Sounder volume	85 dB
----------------	-------

**Standards**

Number of homologation to standard EC	1772-CPD-008344
Q-Label certification	No

**Use conditions**

Operating temperature	-10...55 °C
-----------------------	-------------