



TG501B

## Mains powered smoke detector - silver

### Technical properties

#### Functions

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m

#### Connectivity

Connection mode	hard-wired
-----------------	------------

#### Dimensions

Dimensions (LLxwwxhh)	125 mm x 48 mm
-----------------------	----------------

#### Measurement

Detection Range	50 m <sup>2</sup>
-----------------	-------------------

#### Battery

life of battery	Powered by the main, 10 years battery back up
Weak battery warning	Yes

#### Power supply

Supply Voltage	Mains / alkaline battery 9V 6LR61
----------------	-----------------------------------

#### Scope of delivery

Rechargeable battery backup included	No
--------------------------------------	----

#### Equipment

Sounder volume	85 dB
----------------	-------

#### Standards

Number of homologation to standard EC	1772-CPD-008344
Q-Label certification	No

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------