



TG501C

Mains powered smoke detector - brown

Technical properties

Functions

Operating type	Stand alone
Built-in sounder	Yes, 85 dB at 3 m

Connectivity

Connection mode	hard-wired
-----------------	------------

Dimensions

Dimensions (LLxwxh)	125 mm x 48 mm
---------------------	----------------

Measurement

Detection Range	50 m ²
-----------------	-------------------

Battery

life of battery	Powered by the main, 10 years battery back up
-----------------	---

Power supply

Supply Voltage	Mains / alkaline battery 9V 6LR61
----------------	-----------------------------------

Scope of delivery

Rechargeable battery backup included	No
--------------------------------------	----

Equipment

Sounder volume	85 dB
----------------	-------

Standards

Number of homologation to standard EC	1772-CPD-008344
Q-Label certification	No

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------