



TGA200



Power supply 24 V DC 1A

Technical properties

Configuration

Number of modules	4
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	24 V
Filtered output voltage	24V +/- 5%

Electric current

Output current	1 A
----------------	-----

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Width of installed product	72 mm

Power

Current consumption	150 mA
Power consumed	16 VA
Power consumption (standby)	0.2 W
Total power loss under IN	15 W

Measurement

Voltage measurement range	22.8 to 25.2 V
---------------------------	----------------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey

Installation, mounting

Modular version	Yes
Suitable for front mounting	No

Connection

Type of connection	Quickconnect
--------------------	--------------

Equipment

Short-circuit protected	Yes
-------------------------	-----

Use

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No