



TGA200



Power supply 24 V DC 1A

Technical properties

Architecture

Bus system	EIB
------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	24 V DC
Output voltage	24 V
Filtered output voltage	24V +/- 5%

Electric current

Output current	1 A
----------------	-----

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Width of installed product	72 mm

Power

Current consumption	150 mA
Power consumed	16 VA
Power consumption (standby)	0.2 W
Total power loss under IN	15 W

Measurement

Voltage measurement range	22.8 to 25.2 V
---------------------------	----------------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Installation, mounting

Modular version	Yes
Suitable for front mounting	No

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²

Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect
Equipment	
Short-circuit protected	Yes
Use	
Differentiation characteristic 1 - Sales	with labelling field
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No