



TGC600

## Wall mounting accessory for 4 module width modular device

### Technical properties

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Dimensions

Depth of installed product	89 mm
Internal depth	85 mm
Height of installed product	157 mm
Width of installed product	104 mm
Width in division units	4
Height	157 mm

#### Cover, door

Hinged covers	with transparent hinged cover
Cover type	Closed (plain)
Door locking	without
Cover type	Door
Transparent cover or door	Yes

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

#### Equipment

Number of rows	1
Modular expandability	No
Can be accessorized	No

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

#### Identification

Main design line	KNX
------------------	-----