



TGC600

Wall mounting accessory for 4 module width modular device

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Depth of installed product	89 mm
Internal depth	85 mm
Height of installed product	157 mm
Width of installed product	104 mm
Width in division units	4
Height	157 mm

Cover, door

Hinged covers	with transparent hinged cover
Cover type	Closed (plain)
Door locking	without
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Equipment

Number of rows	1
Modular expandability	No
Can be accessorized	No

Safety

Protection index IP	IP31
---------------------	------

Use conditions

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Identification

Main design line	KNX
------------------	-----