



TN714

### RJ45 patch cable Cat.6 S/FTP, 1m

#### Technical properties

##### Materials

|  |       |
|--|-------|
| Colour   | black |
| Colour anti-kink sleeve                              | black |
| Material connector of connector housing connection 1 | Metal |
| Material connector of connector housing connection 2 | Metal |

##### Connection

|                                |                        |
|--------------------------------|------------------------|
| Type of connector connection 1 | RJ45 8(8)              |
| Type of connector connection 2 | RJ45 8(8)              |
| Case connector connection 1    | IEC 61076-3-106 Var. 1 |
| Case connector connection 2    | IEC 61076-3-106 Var. 1 |

##### Cable

|                    |                      |
|--------------------|----------------------|
| Line length        | 1 m                  |
| AWG range          | AWG 27-7             |
| Cable type         | RJ45/R45 Patch cable |
| Cable construction | 4x2                  |

##### Use

|                |     |
|----------------|-----|
| Pin assignment | 1:1 |
|----------------|-----|

##### Safety

|                     |              |
|---------------------|--------------|
| Anti-kink sleeve    | moulded-on   |
| Protection index IP | IP20         |
| Flame propagation   | EN 50265-2-1 |