



TRB302A



2 flush mounted battery inputs

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Bus module detachable No

Connectivity

Radio protocol KNX Radio

Voltage

Input voltage 5 V

Operating voltage 3 V DC

Electric current

Number of entry circuits 2

Intensity by input 0.03 mA

Dimensions

Dimensions (LLxwwxhh) 48 x 53 x 30 mm

Frequency

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

Length

Max distance to switches 5 mm

Power

Total power loss under IN 0.4 W

Radio transmission power < 10 mW

Measurement

Input scanning voltage per channel 5 V

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Connection

Connection to push-button / switch

Use

Pulse time

min. 50 ms

Safety

Protection index IP

IP30

Use conditions

Operating temperature

0...45 °C